

941 SENSORS AND ACTUATORS

WC PULLCORD WITH CANCELLATION IP65



Code : **9410105**

Model : **LLC-123**

Description

Bathroom peripheral with 1.8m call pull cord, 0.4m cancellation pull cord and red LED for installation in humid environments (showers, saunas, etc.). It allows the patient to launch a call by pulling call pull cord and nurse to cancel a call by pulling cancellation pull cord. Once the patient call has initiated a red LED allows easy identification of call state. It has an anti-strangulation mechanism to release the pull call mechanism preventing accidents and breakage of the device. It has a red pull at the bottom of call pull cord which allows the patient easy location of the pull. Flush mounting with universal box.

Specifications

| | |
|-------------------------------------|---|
| Call pull-cord | Switch type: reed contact |
| | Length: 1,8 m PVC antibacterial color red (RAL 3005 , wine red) |
| | Anti-strangulation mechanism 6Kg |
| | Pull cord pull red (RAL 3005, red wine) |
| Cancellation pull-cord | Switch type: reed contact |
| | Length: 0,4 m PVC antibacterial color green (RAL 6018 , yellow green) |
| | Anti-strangulation mechanism 6Kg |
| | Pull cord pull green (RAL 6018, yellow green) |
| Power supply | 24 VDC |
| Consumption (standby) | 0 mA |
| Consumption (switch activation) | 125 mA |
| Dimensions (width x height x depth) | 80 x 80 x 20 mm |
| Weight | 130g |
| Material | ABS / Polycarbonate |
| Color (trim) | White (RAL 9010, pure white) |
| Operating temperature | -5°C...55°C |
| Protection degree | IP 66 |
| Cleaning | Resistant to cleaning agents according to EN 13727 |
| Mounting | Mounted (standard box, installation depth 38mm ACC-100 / ACC-101) |
| Approvals | CE |