

## 941

## SENSORS AND ACTUATORS

## **CEILING PULL CORD FOR TOILET**



Code: 9415056

Model : **LLC-829** 

Ceiling mounted bathroom pull cord with an antibacterial coating. Designed for emergency requests initiated by the patients. Composed by a simple 2-meter-long cable, with a ceiling mount installation design. This device allows the patient to initiate an emergency call that can be, subsequently, once request attended, canceled by the facility team, by pressing a device installed at the door similar to the LLC-830.

LLC-829 has a safety mechanism that protects the patient from any sort of strangulation. It works by detaching the pull cord once a certain weight applied on it is exceeded. The detached part can be re-attached.

This device can be surface or flush mounted.




| CODIGO/ CODE/ CODE  | 9410349, 9410350<br>9410361, 9415056   | 9410368, 9410369<br>9415015 |  |
|---|--|-----------------------------|--|
| MODELO/ MODEL/ MODÈLE   | LLC-82X  | LLC-92X                     |  |
| Tirador<br>Pull Cord<br>Tirette   | Longitud, Length, Longueur: 2m<br>Color: Rojo, Color: Red, Couleur: Rouge<br>Mecanismo de 6Kg de anti-estrangulamiento; 6kg anti strangle mechanism;<br>Mécanisme de 6kg anti-étranglement |                             |  |
| Pulsador<br>Push button<br>Bouton   | Verde, Green, Vert: ,LLC-X24<br>Rojo, Red, Rouge: LLC-X20, LLC-X21, LLC-X24  |                             |  |
| Alimentación<br>Power supply<br>Alimentation électrique                           | 24V  |                             |  |
| Consumo (stand by)<br>Energy consumption (stand by)<br>Consommation (stand by)    | 10 mA  |                             |  |
| Consumo (máx.)<br>Energy consumption (max.)<br>Consommation (max.)                | 40 mA  |                             |  |
| Dimensiones<br>Size<br>Dimensions   | 80x80x10mm   |                             |  |
| Peso<br>Weight<br>Poids   | O,08Kg   |                             |  |
| Material<br>Material<br>Matériel  | ABS/Polycarbonate/Polycarbonate  |                             |  |
| Color<br>Color<br>Couleur   | Blanco, White, Blanc (RAL 9001)  |                             |  |
| Temperatura operacional<br>Operating temperature<br>Température de fonctionnement | 5°C - 55°C   |                             |  |
| Indice de protección<br>Protection<br>Indice de Protection                        | IP 55  |                             |  |
| Instalación<br>Mounting<br>Installation   | Empotrado, Embedded, Encastré (ACC-100 / ACC-101)<br>En superficie, On surface, En saillie (ACC-110)   |                             |  |



| CODIGO/ CODE/ CODE   | 9410349, 9410350<br>9410361, 9415056 | 9410368, 9410369<br>9415015 |  |
|--|--------------------------------------|-----------------------------|--|
| MODELO/ MODEL/ MODÈLE  | LLC-82X                              | LLC-92X                     |  |
| Normativa (seguridad y accesibilidad)<br>Normative (security and accessibility)<br>Norme (sécurité et accessibilité) | EN 60950-1:2006<br>CTE DB-SUA:2019   |                             |  |
| Normativa (emisiones electromagneticas)<br>Normative (electromagnetic emissions)<br>Norme (champs magnétique)        | EN 61000-3-3                         |                             |  |
| Conector de red<br>Net Connector<br>Connexion  | Bornas, Contact: 82X                 | RJ45: LLC-92X               |  |

## ESQUEMA/SCHEMA/SCHEME



|    | ES                  | EN                | FR               | I/O*   |
|----|---------------------|-------------------|------------------|--------|
| A1 | _                   | _                 | _                |        |
| A2 | Tirador de llamada  | Call pull cord    | Tirette d'appel  | Input  |
| A3 | _                   | _                 | _                |        |
| A4 | _                   | _                 | _                |        |
| B1 | Luz roja            | Red light         | Lumière rouge    | Output |
| B2 | Pulsador de llamada | Call button       | Boutton d'apell  | Input  |
| B3 | GND                 | GND               | Masse            |        |
| B4 | Alimentación 24 V   | Power supply 24 V | Alimentation 24V |        |

- \* Consultar MANAGER para ver el número de borna correspondiente.
- \* Check MANAGER to see the corresponding terminal number.
- \* Consulter MANAGER pour voir le numéro chaque borne.

LLC-820